

# LC BODY

## WITH M24X1 THREAD

The new M24X1 LC Body will allow for customers to easily add quick disconnect functionality to M24 female threads. This thread is commonly found in metric plumbing and faucets.

**APPLICATIONS:** General Purpose, Plumbing

### KEY FEATURES:

- **Male M24X1 thread:** Type is commonly found on European faucets.
- **Brass material:** Durable construction withstands high pressures and temperatures.
- **Compatibility:** This LC body is compatible with LC, PLC® and PLC12.
- **Chrome plating:** Attractive appearance.



[cpcworldwide.com/LC](http://cpcworldwide.com/LC)



**PART NUMBER:** LC10M24

### SPECIFICATIONS:

**Pressure:** Vacuum to 250 PSI

**Temperature:** -40°F to 180°F (-40°C to 82°C)

**Flow:** 2.8 Cv (mated with LC22006)

### MATERIALS:

**Main body components:** Chrome plated brass



**WARRANTY:** All sales are subject to Colder Products Company's limited express warranty set forth in the CPC catalog. Visit [cpcworldwide.com/warranty](http://cpcworldwide.com/warranty) for more information.

**WARNING:** Please note that all sales are subject to CPC's standard Terms and Conditions of Sale. It is the customer's sole obligation to determine the most suitable product for its application, and CPC has no obligation or liability whatsoever in this regard.

© 2026 BY COLDER PRODUCTS COMPANY. CPC, Colder Products Company, and Colder Products are registered trademarks with the United States Patent and Trademark Office. For detailed trademark information, please visit: [cpcworldwide.com/trademarks](http://cpcworldwide.com/trademarks)