

MPC

SERIES CONNECTORS

MPC Series Connectors add ease of use and security to critical fluid handling applications. Choose from a full line of connectors and configurations, including pressure sealing caps and plugs, in sizes to fit 1/8" to 3/8" tubing. MPC couplings offer optional locking sleeves to further guard against accidental disconnects. In addition, coupling halves can be rotated when connected to reduce tube kinks.

SPECIFICATIONS

OPERATING PRESSURE

Vacuum to 60 psi, 4.1 bar

OPERATING TEMPERATURE

Polycarbonate:

-40°F to 250°F (-40°C to 121°C)

Polysulfone:

-40°F to 300°F (-40°C to 149°C)

STERILIZATION

Gamma: Up to 50 kGy irradiation

Autoclave:

Polycarbonate: Up to 250°F (121°C),
30 minutes, up to 10 repetitions

Sterilize uncoupled only

Polysulfone: Up to 270°F (132°C),

60 minutes, up to 25 repetitions

Sterilize uncoupled only

TERMINATIONS

1/8" to 3/8" ID (3.2mm to 9.5mm)

MATERIALS

Main components:

Polycarbonate (purple tint)

Polysulfone (amber tint)

Locking sleeves:

Polysulfone (white)

Thumb Latches:

Polycarbonate (white)

PVDF (white)

O-rings:

Silicone (clear), platinum-cured

WARNING: Pressure, temperature, chemicals, and operating environment can affect the performance of couplings. It is the customer's responsibility to test the suitability of CPC's products in their own application conditions.

FEATURES

Ergonomic thumb latch

BENEFITS

Easy to operate – even with gloved hands

Parting line-free hose barb

Prevent potential leak path

Optional locking sleeve

Prevents accidental disconnection

Various options on termination
size and material

Better flexibility to fit more applications

TYPICAL FLOW RATE

Cv Value Range: 0.1 - 8

for MPC hose barb terminations

Cv values represent the approximate expected flow rate in gallons per minute of water at room temperature for a 1 PSI pressure drop. The flow is generally constrained by the smallest diameter, which in some cases will be the termination diameter and not the Nominal Flow Path.

NOTE

Validation and Extractables data can be requested at cpcworldwide.com/MPC

DID YOU KNOW

The MPC and MPX connectors are perfect for smaller bag systems for aliquoted media or other product stored in bags.

Scan code to visit webpage



cpcworldwide.com/MPC



COLDER PRODUCTS COMPANY

U.S.A.

PHONE: +1 (651) 645-0091

TOLL FREE: +1 (800) 519-7633

E-MAIL: info@cpcworldwide.com

COLDER PRODUCTS COMPANY GMBH

Germany

E-MAIL: cpcgmbh@cpcworldwide.com

DOVER (SHANGHAI) INDUSTRIAL CO., LTD

Shanghai, China

PHONE: +86 21 2411 2666

TOLL FREE: +86 400 990 1978

E-MAIL: asiapacific@cpcworldwide.com

MPC SERIES DIMENSIONS

COUPLING BODIES

	TERMINATION	METRIC EQ.	POLYCARBONATE PART NO.	POLYSULFONE PART NO.	A	B
	1/8" HOSE BARB	3.2 mm ID	MPC17002T03	MPC17002T39	0.96" (24.4 mm)	1.10" (27.9 mm)
	1/4" HOSE BARB	6.4 mm ID	MPC17004T03	MPC17004T39	0.96" (24.4 mm)	1.30" (33.0 mm)
	3/8" HOSE BARB	9.5 mm ID	MPC17006T03	MPC17006T39	0.96" (24.4 mm)	1.30" (33.0 mm)
	1/8" HOSE BARB W/ LOCK	3.2 mm ID	MPCK17002T03	MPCK17002T39	1.02" (25.9 mm)	1.10" (27.9 mm)
	1/4" HOSE BARB W/ LOCK	6.4 mm ID	MPCK17004T03	MPCK17004T39	1.02" (25.9 mm)	1.30" (33.0 mm)
	3/8" HOSE BARB W/ LOCK	9.5 mm ID	MPCK17006T03	MPCK17006T39	1.02" (25.9 mm)	1.30" (33.0 mm)

COUPLING INSERTS

	TERMINATION	METRIC EQ.	POLYCARBONATE PART NO.	POLYSULFONE PART NO.	A	B
	1/8" HOSE BARB	3.2 mm ID	MPC22002T03M	MPC22002T39M	0.60" (15.2 mm)	1.09" (27.7mm)
	1/4" HOSE BARB	6.4 mm ID	MPC22004T03M	MPC22004T39M	0.60" (15.2 mm)	1.30" (33.0 mm)
	3/8" HOSE BARB	9.5 mm ID	MPC22006T03M	MPC22006T39M	0.60" (15.2 mm)	1.30" (33.0 mm)

SEALING COMPONENTS

	SEALING CAP	W/LOCK	MATERIAL	A	B
	MPC32003	MPCK32003	Polycarbonate	0.96" (24.4 mm)	1.30" (33.0 mm)
	MPC32039	MPCK32039	Polysulfone	0.99" (25.2 mm)	1.30" (33.0 mm)
	SEALING PLUG		MATERIAL	A	B
	MPC30003M		Polycarbonate	0.75" (19.1 mm)	1.24" (31.5 mm)
	MPC30039M		Polysulfone	0.75" (19.1 mm)	1.24" (31.5 mm)

PRODUCT DIMENSIONS

